



eXact Color Quick Shake – G/O for Gyroscopic/Oscillating Mixer

Description:

- ✓ Made of Glass Reinforced Nylon
- ✓ 2 Pieces (Bottom & Top)
- ✓ 6 Black Weighted Cartridges to be used for balancing the holder when mixing fewer than 7 cartridges
- ✓ Mix as many as 7 cartridges or as few as 1
- ✓ Mix multiple colors at one time



Easy to Use:

- 1 - Place cartridges in the molded bottom slots
- 2 - Pop the tops off the cartridges
- 3 - Inject paint into the cartridges, twist on caps
- 4 - Place molded top on cartridges
- 5 - Mix for 1-2 minutes
- 6 - Remove caps, add activator, replace caps
- 7 - Replace molded top on cartridges
- 8 - Mix for 1-2 minutes

Voila! eXact color Sealant



10300 E. 107th Place, Brighton, CO, 80601
1-800-289-7290 www.sashco.com