



# eXact color<sup>®</sup> sealant

Tintable Caulk. Just Add Paint.

## eXact color Quick Shake-V for Vortex Shaker

### Description:

- ✓ Made of schedule 80 PVC plastic
- ✓ 1 solid holder with cavities for up to 7 cartridges
- ✓ 1 fiber-reinforced neoprene v-cap with Velcro straps
- ✓ 2 strips Velcro self-adhesive hook material for attachment to the metal mixer basket
- ✓ 6 black weighted cartridges to be used for balancing the holder when mixing fewer than 7 cartridges
- ✓ Mix as many as 7 cartridges or as few as one
- ✓ Mix multiple colors all at one time



### Easy to Use:

- 1 Apply Velcro strips to pail holder
- 2 Insert eXact color cartridges into the v-holder
- 3 Pop tops off the cartridges, inject paint with supplied syringe, twist on caps
- 4 Place v-cap over the cartridges, secure the Velcro straps
- 5 Place v-holder into the paint basket
- 6 Spin for 1-2 minutes
- 7 Twist off caps, add activator, replace caps
- 8 Spin for 1-2 minutes

## Voila! eXact color Sealant



# eXact color<sup>®</sup> sealant

Tintable Caulk. Just Add Paint.

## eXact color Quick Shake-G/O for Gyroscopic/Oscillating Mixer

### Description:

- ✓ Made of glass reinforced nylon
- ✓ 2 pieces (bottom & top)
- ✓ 6 black weighted cartridges to be used for balancing the holder when mixing fewer than 7 cartridges
- ✓ Mix as many as 7 cartridges or as few as one
- ✓ Mix multiple colors all at one time

### Easy to Use:

- 1 Place cartridges in the molded bottom slots
- 2 Pop tops off the cartridges
- 3 Inject paint with supplied syringe, twist on caps
- 4 Place molded top of cartridges
- 5 Mix for 1-2 minutes
- 6 Replace molded top on cartridges
- 8 Mix for 1-2 minutes



**Voila! eXact color Sealant**