



eXact color[®] sealant

Tintable Caulk. Just Add Paint.

eXact color Quick Shake-G/O for Gyroscopic/Oscillating Mixer

Description:

- ✓ Made of glass reinforced nylon
- ✓ 2 pieces (bottom & top)
- ✓ 6 black weighted cartridges to be used for balancing the holder when mixing fewer than 7 cartridges
- ✓ Mix as many as 7 cartridges or as few as one
- ✓ Mix multiple colors all at one time

Easy to Use:

- 1 Place cartridges in the molded bottom slots
- 2 Pop tops off the cartridges
- 3 Inject paint with supplied syringe, twist on caps
- 4 Place molded top of cartridges
- 5 Mix for 1-2 minutes
- 6 Replace molded top on cartridges
- 8 Mix for 1-2 minutes



Voila! eXact color Sealant